


CCMT indexable insert for finishing 30 pieces, HB7130-2, Size: 120408

Order data

Order number	GG3501 120408
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	CCMT 120408
Cutting depth $a_{p \max}$	4.25 mm
Tolerance	M
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Cutting depth a_p	0.2 - 2.5 mm
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	80 - 270 mm/min
Number of changes/inserts	2
Main application	M
Tool material	Carbide
Contents	260066 HB7130-2
Coating	coated
Feed f	0.1 - 0.3 mm/rev.

Quantity	30
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3501 120408