



Boring bar steel, right-hand, Shank \varnothing / insert size: 10/11mm



Order data

Order number	260930 10/11
GTIN	4960664541775
Item class	25U

Description

Version:

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

Through-coolant: yes

Shank $\varnothing D_s$: 10 mm

ISO code toolholder: A10L STLCR/L11

Setting angle κ : 95°

suitable indexable insert: TC.. 1102..

Minimum pre-drill $\varnothing D_{min}$: 12 mm

Centre offset L_3 : 6.2 mm

Technical description

Insert size	11 mm
suitable indexable insert	TC.. 1102..
Minimum pre-drill $\varnothing D_{min}$	12 mm
Centre offset L_3	6.2 mm
Insert screw	269022 4
ISO code toolholder	A10L STLCR/L11
Overall length L	140 mm
Clamping height L_2	9 mm
Setting angle κ	95°
Shank $\varnothing D_s$	10 mm

Application type	right-hand
Boring depth up to	5×D
Standard	DIN 8024
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 4	269022 4
Clamping screw	269407
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8