



## Boring bar steel, right-hand, Shank Ø / insert size: 12/11mm



### Order data

Order number	260930 12/11
GTIN	
Item class	25U

### Description

#### Version:

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

### Technical description

Minimum pre-drill Ø $D_{min}$	14 mm
Centre offset $L_3$	7.2 mm
ISO code toolholder	A12M STLCCR/L11
Insert screw	269022 4
suitable indexable insert	TC.. 1102..
Insert size	11 mm
Overall length L	150 mm
Clamping height $L_2$	11 mm
Setting angle $\kappa$	95 degrees
Shank Ø $D_s$	12 mm
Application type	right-hand
Boring depth up to	5×D
Standard	DIN 8024
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Insert screw Type 4	269022 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8