

Garant**CNMG indexable insert for finishing 50 pieces, HB7130-2, Size: 09T304****Order data**

Order number	GG2904 09T304
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Main application	M
Feed f	0.15 - 0.5 mm/rev.
Number of changes/inserts	4
Contents	250050 HB7130-2
Cutting speed v_c main application	80 - 270 mm/min
Cutting depth $a_{p \max}$	3:25 mm
ISO code indexable insert	CNMG 09T304
Quantity	50
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth a_p	0.3 - 2.5 mm

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2904 09T304