

**Value pack CNMG indexable insert medium machining 30 pieces HB7035-2****Order data**

Order number	GG2409 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm
Corner radius	0.8 mm
Contents	250152 HB7035-2
Number of changes/inserts	4
Cutting depth $a_{p \max}$	3.25 mm
Cutting depth a_p	0.3 - 4 mm
Cutting speed v_c main application	120 - 320 mm/min
Main application	P
ISO code indexable insert	CNMG 09T308
Finishing/roughing assignment	Finishing
Tool material	Carbide
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2409 09T308
