


VCMT indexable insert for finishing 30 pieces, HB7140-2, Size: 160404

Order data

Order number	GG3566 160404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	70 - 230 mm/min
Number of changes/inserts	2
Coating	coated
Corner radius	0.4 mm
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \max}$	2.5 mm
ISO code indexable insert	VCMT 160404
Finishing/roughing assignment	Finishing
Contents	261372 HB7140-2
Main application	M
Cutting depth $a_{p \min}$	0.25 mm
Tolerance	M
Tool material	Carbide
Feed f	0.1 - 0.3 mm/rev.

Data sheet

Quantity	30
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3566 160404