



DCMT indexable insert for medium machining 50 pieces, HBT020, Size: 11T302



Order data

Order number	GG3939 11T302
GTIN	4067263095521
Item class	GGN

Technical description

Contents	260503 HBT020
Feed f	0.12 - 0.3 mm/rev.
ISO code indexable insert	DCMT 11T302
Main application	P
Corner radius	0.2 mm
Cutting speed v_c main application	100 - 280 mm/min
Tool material	Carbide
Number of changes/inserts	2
Coating	TiCN
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth $a_{p \min}$	0.15 mm
Cutting depth a_p	0.5 - 2.5 mm

Data sheet

Finishing/roughing assignment	Finishing
Quantity	50
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3939 11T302