



**Turning tool, wide neutral, similar to DIN 4976 (ISO 4), P20/K25, Shank height: 25mm**



## Order data

Order number	296605 25
GTIN	4045197519528
Item class	22E

## Description

### Version:

**Carbide** – steel shanks with 700 - 800 N/mm<sup>2</sup> strength and flat chamfered mounting surface. Fitted with diamond ground carbide inserts. Angles on the inserts are precision ground. All turning tools are supplied with sharp cutting edges. Sharpening the cutting edge with a boron carbide hand lapper will increase the tool edge life. The extent of the wear area is dependent on the cutting conditions. For roughing and interrupted machining it is imperative that the cutting edges are sharpened.

Fitted with diamond ground carbide inserts.

### Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

### Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

## Technical description

Shank height h	25 mm
Blade width	16 mm
Overall length	140 mm
Shank width b	16 mm
Tool material	P20/K25
Type of product	Turning tool

