

**Value pack SNMG indexable insert roughing 50 pieces HB7020-2****Order data**

Order number	GG2453 120408
GTIN	4067263093268
Item class	GGN

Technical description

Finishing/roughing assignment	Roughing
Number of changes/inserts	8
Cutting depth $a_{p \max}$	4.25 mm
Tool material	Carbide
Main application	P
Contents	251324 HB7020-2
ISO code indexable insert	SNMG 120408
Cutting depth $a_{p \min}$	0.55 mm
Corner radius	0.8 mm
Cutting depth a_p	1.5 - 6 mm
Feed f	0.25 - 0.6 mm/rev.
Cutting speed v_c main application	110 - 360 mm/min
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2453 120408
