

**CNMG indexable insert for medium machining 50 pieces, HB7020-2, Size: 160612****Order data**

|              |               |
|--------------|---------------|
| Order number | GG2411 160612 |
| GTIN         | 4067263092407 |
| Item class   | GGN           |

**Technical description**

|                                      |                              |
|--------------------------------------|------------------------------|
| Cutting depth $a_{p \min}$           | 0.8 mm                       |
| Contents                             | 250170 HB7020-2              |
| Corner radius                        | 1.2 mm                       |
| Cutting depth $a_p$                  | 0.3 - 4 mm                   |
| Feed $f$                             | 0.2 - 0.5 mm/rev.            |
| Finishing/roughing assignment        | Finishing                    |
| Main application                     | P                            |
| ISO code indexable insert            | CNMG 160612                  |
| Tool material                        | Carbide                      |
| Cutting depth $a_{p \max}$           | 5.5 mm                       |
| Cutting speed $v_c$ main application | 130 - 370 mm/min             |
| Number of changes/inserts            | 4                            |
| Quantity                             | 50                           |
| Type                                 | HB7020-2                     |
| Cutting conditions                   | slightly interrupted         |
| Chip breaker                         | SM                           |
| Type of product                      | Indexable insert for turning |

---

## Suitable products

No Shop URL available for: GG2411 160612

---