


VCMT indexable insert for finishing 30 pieces, HBT020, Variety: 160404

Order data

Order number	GG3952 160404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Coating	TiCN
Cutting depth a_p	0.4 - 1.5 mm
Feed f	0.1 - 0.3 mm/rev.
Corner radius	0.4 mm
Number of changes/inserts	2
Main application	P
Tool material	Carbide
Cutting depth $a_{p \max}$	2.5 mm
Finishing/roughing assignment	Finishing
Contents	261388 HBT020
Cutting speed v_c main application	120 - 330 mm/min
ISO code indexable insert	VCMT 160404
Quantity	30

Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3952 160404