

**Value pack TNMG indexable insert finishing 30 pieces HB7020-2****Order data**

Order number	GG2461 160404
GTIN	4067263093398
Item class	GGN

Technical description

Tool material	Carbide
Cutting speed v_c main application	130 - 370 mm/min
Cutting depth $a_{p \min}$	0.25 mm
ISO code indexable insert	TNMG 160404
Contents	251542 HB7020-2
Cutting depth a_p	0.3 - 4 mm
Main application	P
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	6
Cutting depth $a_{p \max}$	4 mm
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2461 160404
