

**Hook turning tool right-hand similar to DIN 4963, HSS E, Shank Ø: 10mm****Order data**

Order number	297120 10
GTIN	4045197190642
Item class	22E

Description**Version:**

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

maximum grooving depth t_{\max}	6 mm
for bores from \varnothing	20 mm
Blade width	3 mm
Shank \varnothing	10 mm
Overall length	160 mm
Tool material	HSS E
Type of product	Turning tool