

**Value pack TNMG indexable insert finishing 30 pieces HB7035-2****Order data**

Order number	GG2462 160408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 320 mm/min
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	6
Contents	251244 HB7035-2
Tool material	Carbide
Finishing/roughing assignment	Finishing
ISO code indexable insert	TNMG 160408
Cutting depth $a_{p \min}$	0.55 mm
Main application	P
Cutting depth a_p	0.3 - 4 mm
Corner radius	0.1 mm
Cutting depth $a_{p \max}$	4 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2462 160408
