

**Torque screwdriver, fixed setting, without scale, set torque: 0,6N·m****Order data**

Order number	659890 0,6
GTIN	4069515041737
Item class	62E

Description**Version:**

Torque screwdriver with easy-grip 2-component handle and **fixed torque**. When the set torque is reached the screwdriver triggers, with clearly audible and perceptible signals. Suitable for clockwise tightening. **It is not possible to tighten the screw any further.**

Advantage:

Torque screwdriver can be used with all conventional bits C 6.3 and E 6.3 (similar to No. 675155, 675390).

Application:

For controlled tightening of screws to a pre-set torque.
Ideal for fitting indexable inserts.

Standard:

Tested to **DIN EN ISO 6789**.

Accuracy:

±10% of the specified value.

Note:

All Wiha interchangeable blades (No. 659940 – 659946) can also be used in the HOLEX torque screwdriver No. 659945.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

The set torque value **cannot** be changed.

Technical description

Connection format	Bit holder 1/4 inch
Bit socket	D 6.3

Data sheet

Bit socket	F 6.3
Direction of tightening	Right-hand tightening
Data can be recorded	no
Calibration	O1
Trigger principle	mechanical slip clutch
set torque	0.6 Nm
Setting the trigger value	preset
set torque	60 cNm
Overall length L	168 mm
Torque measuring accuracy	±10 %
Standard	DIN EN ISO 6789
Display	analogue
Feedback	acoustic signal
Feedback	triggering
Measurement process	Torque
Release signalling	acoustic
Release signalling	haptic
Adjustable trigger value	non-adjustable
Measurement technology	mechanical
Torque fixed setting	yes
Type of product	Torque screwdriver

Suitable products

No Shop URL available for: 659890 0,6