

**Torque screwdriver, fixed setting, without scale, set torque: 3,8N·m****Order data**

| | |
|--------------|---------------|
| Order number | 659890 3,8 |
| GTIN | 4069515041812 |
| Item class | 62E |

Description**Version:**

Torque screwdriver with easy-grip 2-component handle and **fixed torque**. When the set torque is reached the screwdriver triggers, with clearly audible and perceptible signals. Suitable for clockwise tightening. **It is not possible to tighten the screw any further.**

Advantage:

Torque screwdriver can be used with all conventional bits C 6.3 and E 6.3 (similar to No. 675155, 675390).

Application:

For controlled tightening of screws to a pre-set torque.
Ideal for fitting indexable inserts.

Standard:

Tested to **DIN EN ISO 6789**.

Accuracy:

±10% of the specified value.

Note:

All Wiha interchangeable blades (No. 659940 – 659946) can also be used in the HOLEX torque screwdriver No. 659945.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

The set torque value **cannot** be changed.

Technical description

| | |
|-------------------------|-----------------------|
| Direction of tightening | Right-hand tightening |
| Standard | DIN EN ISO 6789 |

Data sheet

| | |
|---------------------------|------------------------|
| Calibration | O1 |
| Data can be recorded | no |
| Setting the trigger value | preset |
| Measurement technology | mechanical |
| Adjustable trigger value | non-adjustable |
| Feedback | acoustic signal |
| Feedback | triggering |
| Connection format | Bit holder 1/4 inch |
| set torque | 380 cNm |
| Torque measuring accuracy | ±10 % |
| Release signalling | acoustic |
| Release signalling | haptic |
| Measurement process | Torque |
| Bit socket | D 6.3 |
| Bit socket | F 6.3 |
| Overall length L | 168 mm |
| Trigger principle | mechanical slip clutch |
| set torque | 3.8 Nm |
| Display | analogue |
| Torque fixed setting | yes |
| Type of product | Torque screwdriver |

Suitable products

No Shop URL available for: 659890 3,8