

**TNMG indexable insert for medium machining 50 pieces, HB7020-2, Size: 160404****Order data**

Order number	GG2464 160404
GTIN	4067263093404
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	4 mm
Contents	251542 HB7020-2
Cutting depth a_p	0.3 - 4 mm
Corner radius	0.4 mm
Tool material	Carbide
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	6
ISO code indexable insert	TNMG 160404
Main application	P
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	130 - 370 mm/min
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2464 160404
