

**Value pack VNMG indexable insert finishing 30 pieces HB7010-2****Order data**

Order number	GG2466 160404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2 mm
ISO code indexable insert	VNMG 160404
Main application	P
Cutting speed v_c main application	170 - 500 mm/min
Number of changes/inserts	4
Contents	251732 HB7010-2
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	2.5 mm
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.4 mm
Tool material	Carbide
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2466 160404
