

Garant**VCMT indexable insert for finishing 50 pieces, HB7140-2, Size: 160402****Order data**

Order number	GG3569 160402
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting depth $a_{p \min}$	0.15 mm
Contents	261370 HB7140-2
Main application	M
Number of changes/inserts	2
Coating	coated
Cutting depth $a_{p \max}$	2.5 mm
Cutting speed v_c main application	70 - 230 mm/min
Tolerance	M
ISO code indexable insert	VCMT 160402

Quantity	50
Feed f	0.1 - 0.3 mm/rev.
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3569 160402