

Garant**CNMG indexable insert for medium machining 50 pieces, HB7140-2, Size: 120408****Order data**

Order number	GG2911 120408
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.8 mm
Quantity	50
Tolerance	M
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 4 mm
Finishing/roughing assignment	Finishing
Contents	250158 HB7140-2
Cutting depth $a_{p\ max}$	4:25 mm
Main application	M
Number of changes/inserts	4
Coating	coated
Tool material	Carbide
Cutting speed v_c main application	60 - 200 mm/min

Data sheet

ISO code indexable insert	CNMG 120408
Cutting depth $a_{p\ min}$	0.55 mm
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2911 120408