

Garant**VCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 160408****Order data**

Order number	GG3571 160408
GTIN	4067263097259
Item class	GGN

Technical description

Main application	M
Cutting speed v_c main application	70 - 240 mm/min
Tolerance	M
Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.8 mm
Tool material	Carbide
Contents	261459 HB7130-2
Cutting depth $a_{p \max}$	2.5 mm
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth a_p	0.5 - 2.5 mm
Number of changes/inserts	2
ISO code indexable insert	VCMT 160408
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3571 160408