

**TCMT 16T304, Grade: HB7140****Order data**

Order number	260956 HB7140
GTIN	4045197670809
Item class	21G

Description

TCMT 16T304 HB7140 Grade: HB7140
Chip breaker: V4S
Cutting depth a_p : 0.5 - 3 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 85 - 210 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	neutral
Rake	degrees
Indexable insert profile	
Type of product	