

Garant**CNMG indexable insert for roughing 30 pieces, HB7130-2, Size: 120408****Order data**

Order number	GG2913 120408
GTIN	4067263094036
Item class	GGN

Technical description

Corner radius	0.8 mm
Cutting speed v_c main application	60 - 220 mm/min
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth $a_{p \max}$	4:25 mm
Finishing/roughing assignment	Roughing
Cutting depth a_p	1.5 - 6 mm
Number of changes/inserts	4
Tool material	Carbide
Quantity	30
Feed f	0.25 - 0.6 mm/rev.
ISO code indexable insert	CNMG 120408
Main application	M
Contents	250322 HB7130-2
Type	HB7130-2

Cutting conditions	slightly interrupted
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2913 120408