

**WNMG indexable insert for finishing 50 pieces, HB7020-2, Size: 080408****Order data**

|              |               |
|--------------|---------------|
| Order number | GG2482 080408 |
| GTIN         | 4067263092278 |
| Item class   | GGN           |

**Technical description**

|                                      |                              |
|--------------------------------------|------------------------------|
| ISO code indexable insert            | WNMG 080408                  |
| Cutting depth $a_{p \min}$           | 0.55 mm                      |
| Finishing/roughing assignment        | Finishing                    |
| Main application                     | P                            |
| Number of changes/inserts            | 6                            |
| Cutting depth $a_p$                  | 0.3 - 2 mm                   |
| Contents                             | 251964 HB7020-2              |
| Feed $f$                             | 0.1 - 0.4 mm/rev.            |
| Cutting speed $v_c$ main application | 160 - 400 mm/min             |
| Tool material                        | Carbide                      |
| Corner radius                        | 0.8 mm                       |
| Cutting depth $a_{p \max}$           | 2.75 mm                      |
| Quantity                             | 50                           |
| Type                                 | HB7020-2                     |
| Cutting conditions                   | slightly interrupted         |
| Chip breaker                         | SS                           |
| Type of product                      | Indexable insert for turning |

## Suitable products

No Shop URL available for: GG2482 080408

---