

**CNMG indexable insert for roughing 30 pieces, HB7130-2, Size: 160608****Order data**

Order number	GG2913 160608
GTIN	4067263094098
Item class	GGN

Technical description

Tool material	Carbide
Feed f	0.25 - 0.6 mm/rev.
Coating	coated
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.55 mm
Quantity	30
Cutting depth a_p	1.5 - 6 mm
Main application	M
Corner radius	1.2 mm
Contents	250334 HB7130-2
Cutting speed v_c main application	60 - 220 mm/min
ISO code indexable insert	CNMG 160612
Cutting depth $a_{p \max}$	4:25 mm
Finishing/roughing assignment	Roughing

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2913 160608