



CCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 09T302



Order data

Order number	GG3507 09T302
GTIN	4067263096139
Item class	GGN

Technical description

Tool material	Carbide
Cutting speed v_c main application	70 - 240 mm/min
Finishing/roughing assignment	Finishing
Tolerance	M
Cutting depth $a_{p \max}$	3.25 mm
Number of changes/inserts	2
ISO code indexable insert	CCMT 09T302
Main application	M
Contents	260148 HB7130-2
Corner radius	0.2 mm
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.2 - 4 mm
Coating	coated
Cutting depth $a_{p \min}$	0.25 mm

Data sheet

Quantity	30
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3507 09T302