

**Value pack WNMG indexable insert medium machining 30 pieces HB7035-2****Order data**

Order number	GG2486 080412
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.8 mm
Cutting depth $a_{p \min}$	0.55 mm
Main application	P
Contents	252072 HB7035-2
ISO code indexable insert	WNMG 080412
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	6
Cutting speed v_c main application	120 - 320 mm/min
Tool material	Carbide
Cutting depth $a_{p \max}$	2 mm
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 4 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2486 080412
