

Garant**CCMT indexable insert for medium machining 50 pieces, HB7130-2, Size: 060202****Order data**

Order number	GG3510 060202
GTIN	4067263096108
Item class	GGN

Technical description

Quantity	50
Cutting speed v_c main application	70 - 240 mm/min
ISO code indexable insert	CCMT 060202
Corner radius	0.2 mm
Main application	M
Number of changes/inserts	2
Cutting depth $a_{p \text{ min}}$	0.15 mm
Contents	260140 HB7130-2
Tool material	Carbide
Tolerance	M
Cutting depth $a_{p \text{ max}}$	2 mm
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing

Data sheet

Cutting depth a_p	0.2 - 4 mm
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3510 060202