

Garant**DCMT indexable insert for medium machining 50 pieces, HB7020-2, Size: 11T304****Order data**

Order number	GG2823 11T304
GTIN	4067263095460
Item class	GGN

Technical description

Corner radius	0.4 mm
Contents	260462 HB7020-2
Cutting depth $a_{p \max}$	2.75 mm
Cutting speed v_c main application	110 - 350 mm/min
Main application	P
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	DCMT 11T304
Tool material	Carbide
Feed f	0.08 - 0.3 mm/rev.
Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	2

Data sheet

Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2823 11T304