

Garant**DNMG indexable insert for finishing 50 pieces, HB7130-1, Size: 110404****Order data**

Order number	GG2921 110404
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	4
Cutting depth a_p	0.3 - 2 mm
Feed f	0.1 - 0.4 mm/rev.
ISO code indexable insert	DNMG 150608
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Quantity	50
Tool material	Carbide
Cutting speed v_c main application	90 - 290 mm/min
Contents	250652 HB7120-1
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	2.75 mm
Main application	M

Type	HB7130-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2921 110404