



CCMT indexable insert for medium machining 50 pieces, HBT130, Size: 120404



Order data

Order number	GG2625 120404
GTIN	4067263096306
Item class	GGN

Technical description

Number of changes/inserts	2
ISO code indexable insert	CCMT 120404
Finishing/roughing assignment	Finishing
Tool material	Carbide
Corner radius	0.4 mm
Feed f	0.05 - 0.35 mm/rev.
Coating	TiCN
Cutting depth $a_{p \min}$	0.25 mm
Cutting speed v_c main application	50 - 200 mm/min
Contents	260219 HBT130
Quantity	50
Cutting depth a_p	0.3 - 3 mm
Main application	M

Data sheet

Cutting depth $a_{p \max}$	4.25 mm
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2625 120404