


SCMT indexable insert for finishing 30 pieces, HB7010-2, Size: 120408

Order data

Order number	GG2827 120408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	150 - 500 mm/min
Contents	260750 HB7010-2
Finishing/roughing assignment	Finishing
Main application	P
Corner radius	0.8 mm
Tool material	Carbide
Number of changes/inserts	4
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	SCMT 120408
Cutting depth $a_{p \max}$	4.25 mm
Quantity	30
Type	HB7010-2

Data sheet

Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2827 120408