

**DCMT indexable insert for medium machining 50 pieces, HBT130, Size: 11T302****Order data**

Order number	GG2669 11T302
GTIN	4067263096566
Item class	GGN

Technical description

Main application	M
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2.75 mm
Number of changes/inserts	2
Cutting speed v_c main application	50 - 200 mm/min
Cutting depth $a_{p \min}$	0.15 mm
Contents	260503 HBT130
Feed f	0.05 - 0.35 mm/rev.
Cutting depth a_p	0.3 - 2.5 mm
Tool material	Carbide
ISO code indexable insert	DCMT 11T302
Quantity	50

Coating	TiCN
Corner radius	0.2 mm
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2669 11T302