



DCMT indexable insert for medium machining 50 pieces, HBT130, Size: 11T308



Order data

Order number	GG2669 11T308
GTIN	4067263096603
Item class	GGN

Technical description

ISO code indexable insert	DCMT 11T308
Corner radius	0.8 mm
Tool material	Carbide
Number of changes/inserts	2
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth a_p	0.3 - 2.5 mm
Feed f	0.05 - 0.35 mm/rev.
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	50 - 200 mm/min
Contents	260508 HBT130
Coating	TiCN

Quantity	50
Main application	M
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2669 11T308