



SCMT indexable insert for medium machining 30 pieces, HBT130, Size: 09T304



Order data

Order number	GG2674 09T304
GTIN	4067263096696
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	3.25 mm
Feed f	0.05 - 0.35 mm/rev.
ISO code indexable insert	SCMT 09T304
Main application	M
Number of changes/inserts	4
Cutting depth a_p	0.3 - 2.5 mm
Contents	260791 HBT130
Cutting speed v_c main application	50 - 200 mm/min
Corner radius	0.4 mm
Tool material	Carbide
Coating	TiCN
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Quantity	30

Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2674 09T304