



TCMT indexable insert for medium machining 30 pieces, HBT130, Size: 16T304



Order data

Order number	GG2684 16T304
GTIN	4067263096955
Item class	GGN

Technical description

Corner radius	0.4 mm
Coating	TiCN
Cutting depth $a_{p \max}$	4 mm
Tool material	Carbide
Cutting speed v_c main application	50 - 200 mm/min
Contents	261018 HBT130
Cutting depth a_p	0.3 - 2.5 mm
Main application	M
Number of changes/inserts	3
ISO code indexable insert	TCMT 16T304
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.35 mm/rev.
Quantity	30

Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2684 16T304