

**DCMT indexable insert for finishing 30 pieces, HB7140-2, Size: 11T308****Order data**

Order number	GG3515 11T308
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	DCMT 11T308
Tool material	Carbide
Cutting speed v_c main application	70 - 230 mm/min
Cutting depth $a_{p \max}$	2.75 mm
Number of changes/inserts	2
Contents	260361 HB7140-2
Corner radius	0.8 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.2 - 1.5 mm
Main application	M
Finishing/roughing assignment	Finishing
Coating	coated
Cutting depth $a_{p \min}$	0.55 mm
Tolerance	M

Quantity	30
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3515 11T308