


RCG. indexable insert for medium machining 30 pieces, HU730-1, Size: 0803

Order data

Order number	GG3819 0803
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.5 mm
Main application	N
Feed f	0.1 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
ISO code indexable insert	RCGT 0803
Cutting speed v_c main application	350 - 600 mm/min
Tolerance	G
Tool material	Carbide
Number of changes/inserts	2
Coating	uncoated
Cutting depth a_p	0.5 - 2 mm
Cutting depth $a_{p \max}$	2 mm
Contents	260630 HU7310-1
Quantity	30

Type	HU730-1
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3819 0803