

**TCMT indexable insert for finishing 30 pieces, HB7010-2, Size: 110202****Order data**

Order number	GG2839 110202
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.4 mm
Number of changes/inserts	3
Cutting speed v_c main application	150 - 500 mm/min
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth a_p	0.2 - 1.5 mm
Contents	260950 HB7010-2
Tool material	Carbide
ISO code indexable insert	TCMT 110202
Main application	P
Feed f	0.07 - 0.25 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7010-2

Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2839 110202