

Garant**DNMG indexable insert for roughing 50 pieces, HB7120-1, Size: 150608****Order data**

Order number	GG2933 150608
GTIN	4067263092278
Item class	GGN

Technical description

Contents	250862 HB7120-1
Corner radius	0.8 mm
Tool material	Carbide
Finishing/roughing assignment	Finishing
Cutting depth a_p	1.5 - 6 mm
Quantity	50
Number of changes/inserts	4
ISO code indexable insert	DNMG 150608
Main application	M
Cutting depth $a_{p \max}$	3.75 mm
Cutting speed v_c main application	70 - 240 mm/min
Feed f	0.25 - 0.6 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm

Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2933 150608