

Garant**TCMT indexable insert for finishing 50 pieces, HB7010-2, Size: 110202****Order data**

Order number	GG2842 110202
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	3
Contents	260950 HB7010-2
Main application	P
Cutting depth $a_{p \min}$	0.25 mm
Quantity	50
Corner radius	0.4 mm
Cutting depth a_p	0.2 - 1.5 mm
Finishing/roughing assignment	Finishing
Feed f	0.07 - 0.25 mm/rev.
Cutting speed v_c main application	150 - 500 mm/min
Cutting depth $a_{p \max}$	2.75 mm
Tool material	Carbide
ISO code indexable insert	TCMT 110202

Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2842 110202