

Garant**KNUX indexable insert for medium machining 50 pieces, HB7130-2, Size: 160405R****Order data**

Order number	GG2937 160405R
GTIN	4067263094487
Item class	GGN

Technical description

Coating	coated
Quantity	50
Main application	M
Finishing/roughing assignment	Finishing
ISO code indexable insert	KNUX 160405R
Cutting depth $a_{p \min}$	0.35 mm
Corner radius	0.5 mm
Tool material	Carbide
Number of changes/inserts	2
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \max}$	4 mm
Cutting depth a_p	0.5 - 5 mm
Contents	251030 HB7130-2

Data sheet

Cutting speed v_c main application	70 - 240 mm/min
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2937 160405R