

Garant**KNUX indexable insert for medium machining 50 pieces, HB7130-2, Size: 160410R****Order data**

Order number	GG2937 160410R
GTIN	4067263094524
Item class	GGN

Technical description

Tool material	Carbide
Cutting depth a_p	0.5 - 5 mm
Contents	251036 HB7130-2
Finishing/roughing assignment	Finishing
Corner radius	1 mm
Quantity	50
Cutting speed v_c main application	70 - 240 mm/min
Number of changes/inserts	2
Cutting depth $a_{p \max}$	4 mm
Feed f	0.2 - 0.5 mm/rev.
ISO code indexable insert	KNUX 160410R
Cutting depth $a_{p \min}$	0.65 mm
Coating	coated

Main application	M
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2937 160410R