

Garant**TCMT indexable insert for finishing 50 pieces, HB7020-2, Size: 110202****Order data**

Order number	GG2843 110202
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	140 - 400 mm/min
Number of changes/inserts	3
Cutting depth a_p	0.2 - 1.5 mm
ISO code indexable insert	TCMT 110202
Main application	P
Quantity	50
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2.75 mm
Feed f	0.07 - 0.25 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Contents	260950 HB7020-2
Tool material	Carbide
Corner radius	0.4 mm

Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2843 110202