

Garant**DCMT indexable insert for medium machining 50 pieces, HB7140-2, Size: 11T308****Order data**

Order number	GG3525 11T308
GTIN	4067263092278
Item class	GGN

Technical description

Quantity	50
Tool material	Carbide
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Feed f	0.1 - 0.4 mm/rev.
Contents	260464 HB7140-2
Cutting speed v_c main application	60 - 200 mm/min
ISO code indexable insert	DCMT 11T308
Tolerance	M
Coating	coated
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth a_p	0.5 - 2.5 mm

Data sheet

Main application	M
Number of changes/inserts	2
Cutting depth $a_{p \max}$	2.75 mm
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3525 11T308