

Garant**RCMX indexable insert for medium machining 50 pieces, HB7130-2, Size: 1204****Order data**

Order number	GG3527 1204
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	RCMX 1204
Cutting speed v_c main application	70 - 240 mm/min
Number of changes/inserts	4
Main application	M
Quantity	50
Cutting depth a_p	0.5 - 2 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2 mm
Tool material	Carbide
Feed f	0.1 - 0.3 mm/rev.
Coating	coated
Contents	260650 HB7130-2
Cutting depth $a_{p \min}$	0.5 mm

Tolerance	M
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3527 1204