

**Garant**

**Side lock arbor Form ADB with cooling channel bores, SK 40 A = 100,  
Clamping range  $\varnothing$  D1: 10mm**


**Order data**

Order number	300235 10
GTIN	4045197463333
Item class	31A

**Description**
**Version:**

With Balluff/RFID chip bore.

**GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	10 mm
Spare clamping screw No. 30 9900	10
Overhang dimension A	100 mm
External $\varnothing$ D	35 mm
Adapter	SK 40 A = 100
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB

Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud sealed suitable for steep tapers 40	308635 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40
	308820 40

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872)  
suitable for ISO taper size 40

Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Spare clamping screw for chucks with clamping $\varnothing$ D1 10 mm	309900 10