

Garant**SNMG indexable insert for medium machining 50 pieces, HB7130-2, Size: 120412****Order data**

Order number	GG2948 120412
GTIN	4067263094685
Item class	GGN

Technical description

Number of changes/inserts	8
Cutting depth $a_{p \max}$	4:25 mm
Main application	M
Cutting speed v_c main application	70 - 240 mm/min
Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	SNMG 120412
Contents	251226 HB7130-2
Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.4 mm/rev.
Quantity	50
Cutting depth a_p	0.5 - 4 mm
Corner radius	1.2 mm
Coating	coated

Tool material	Carbide
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2948 120412