


SCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 09T308

Order data

Order number	GG3531 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.1 - 0.3 mm/rev.
Number of changes/inserts	4
Quantity	50
Main application	M
ISO code indexable insert	SCMT 09T308
Cutting depth $a_{p \max}$	3.25 mm
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 1.5 mm
Contents	260744 HB7120-1
Cutting speed v_c main application	90 - 290 mm/min
Tool material	Carbide

Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3531 09T308