

Garant**Value pack SCMT 09T304****Order data**

Order number	GG3532 09T304
GTIN	4067263092278
Item class	GGN

Description**Version:**

Unbreakable, flexible pressure oiler, of polyethylene with extendable brass discharge tube, rotary closure at the spout tip. Tube guide with adjusting nut.
Resistant to ethanol and isopropanol-based disinfectants.

Technical description

Contents	260742 HB7130-2
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	3.25 mm
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	80 - 270 mm/min
Main application	M
Feed f	0.1 - 0.3 mm/rev.
Number of changes/inserts	4
Cutting depth a_p	0.2 - 1.5 mm

ISO code indexable insert	SCMT 09T304
Tool material	Carbide
Quantity	50
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3532 09T304